DWM AUTOMATIC CHECKWEIGHER

9001



release date 29-01-2016



DWM automatic checkweighers provide the highest quality and weighing accuracy..

They are applied mainly for pharmaceutical and food industry. Using magnetoelectric modules allows to weigh products quickly, providing accuracy of 0,01 g and efficiency 500 items/min. (depending on the product mass and dimensions). The device features a friendly, intuitive interface and several built-in functions that enable the statistical data operation and service process. Checkweighers allow a precise control of packaged products in accordance with the valid regulations. A modular base construction allows a flexible configuration of the device.

Complex communication modules fully integrate the scale with the production line, which makes it possible to operate it automatically. Connecting the checkweigher to the computer system allows to monitor production process on-line, save the weighments, generate the reports considering the weighing statistics, quantitative statistics and the production line failures and stoppages.

DWM automatic checkweighers series are designed to control single goods whose mass does not exceed 7500 g. Scale software enables setting the parameters according to customers regulations or according to the current regulation on Control of Packaged Goods. The flexible limits working mode was designed for pharmaceutical concerns. DWM automatic scales series are attested by NIH.


Main applications:

- Control of goods in accordance with regulation on Control of Packaged Goods
- The full control of production process
- Control over dozing devices
- Control over the products packaging precision
- Weighing medicines, blister packs, syrups, etc.

Technical data:

	DWM 750	DWM 1500	DWM 3000	DWM 7500	
Max capacity	750 g	1500 g	3000 g	7500 g	
Verification unit	0,1 g	0,2 g	0,5 g	1 g	
Reading unit	0,1 g	0,2 g	0,5 g	1 g	
Expanded reading unit	0,05 g	0,1 g	0,1 g	0,5 g	
Min capacity	2 g	4 g	10 g	20 g	
Tare range	-750 g	-1500 g	-3000 g	-7500 g	
Conveyor velocity	1,6 m/s	1,6 m/s	1,6 m/s	1,6 m/s	
Construction	Powder coated steel / stainless steel				
OIML class	XIII(1), Y(a)				
Working temperature	+5° ÷ +40 °C				
Protection level	IP 55/ 65				
Power supply	100 ÷ 240 V AC 50 ÷ 60 Hz				
Display	LCD 12"				
Keyboard	touch screen				
Interfaces	Ethernet, USB, RS 232, I/O				

Accessories: Stacklight/optical signalling device Inkjet printer Product positioning unit Label printer Product infeed unit Line congestion sensor Bin for rejected products Bin overload / rejection sensor Metal detector Pressure failure sensor Report printer Additional conveyor unit



Main panel



Database window

Bazy Raporty	Utsweenis Alarmy	🛞 🍂 Upr	agowany: Anonimowy ewnienia: Administrator a i czas logowania: 2013-11-26 08:27:55
Wejścia Wyjścia Kap	ędy 🕢 Data i czas	Kalibracja 🧼 Poła ekranu	czenia 🥎 Konliguracja 🥩 Ustawie owe wagi
Ustawienia podstawowe	Ustawienia zaawanso	wane Konfiguracja zrzu	tników Okno główne 💶
Język Polski Strona kodowa 1250 (Ał Kalibracja dynamiczna na żądar	VISI - Central Europ V	Start/Stop z wejścia Włączony 🔽 Tnyb Start i Stop 💌	Maksymalna długóść paczki 50 • cm Minimalny odstęp mięży paczki 0 • cm Reakcja na za mały odstęp Zatzymywanie
Logowanie anonimowe	Tryb pracy	Sygnalizator	Zrzucanie 📀
Włączone C	Standard 📀	Włączony 🗖	Sygnał złego towaru
Wagowy C Administrator C	KTP C KTP kryteria własne C	Rodzaj LO-OK-HI	Aktywny Czas działania (ms)
Edytuj uprawnienia wagowego	Kontrola progu T2	Sygnalizacja dźwiękowa awarii Sygnal. dźwiękowa Niko dla MET	Zapiez

Raport OK 179,500 g 158 000 a 123478 filet 158 0.000 a ок 179.500 а Tara 4 szt. 5 2 000 a Ilość LO 1 szt. 30,000 a 0 szt. 2010-07-27 12:58:19 Suma ZŁYCH 302,000 g llość bł 4 szt. 0 szt. 2010.07.27 12:58:35 Suma LO 302,000 g 0.000 a 0.000 a Suma HI **a** 0,0% 179,500 g OK 20.0% Średnia OK LO 80.0%

Configuration panel

Renart window

Lista

🚰 Drukuj



Software:

The checkweigher features an industrial computer and Windows Embedded operating system. This solution allows an intuitive and easy cooperation with the device. The scale and standard office interface are similar, which facilitates the operation.

Database module was designed on the basis of Microsoft SQL Server, which allows a stable and safe saving of data generated by the scale, as well as an easy connection of the database with the client's software. Saving the databases and weighment records on two separate memory carriers provides high security.

All checkweigher elements like drives, rejectors, emergency buttons, warning lights are controlled by the real time controller, which guarantees the flow of work and an instant reaction to the emergency signals.

Checkweighers provide the full exchange of data via Ethernet network. The communication protocol ensures the automatic transfer of weighment records, databases update, introduction of new settings and the device work monitoring in on-line mode.

Functions:

- · Statistical weighing
- · Dynamic weighing
- · Database of operators on different access level
- · Assortment database
- · Weighments database
- · Reports database
- Tresholds control +/-
- Control of goods in accordance with regulation on Control of Packaged Goods
- Control of goods in accordance with customer regulations
- · Autocontrol
- · Automatic correction of the package mass
- · Control of the rejector work accuracy
- The supply installation pressure control
- · Bin overload sensor
- · Cooperation with dozers
- Cooperation with PLC controller
- Reporting
- · Export of reports to PDF files
- · Control of products flow
- · Control of products dimensions
- · Flexible regulation of transporters velocity

ENDEL WEIGH SYSTEMS LLC

1412 AL MANARA Tower, Near JW Marriot Marquis, Business Bay, Dubai, UAE. Phone: +971-4-5645722 | Mobile & S: +971-50-7343742 Email: sales@dubaiweighing.com | Webspace: www.dubaiweighing.com